






Recirculation
HR0003
HR0011
HF4003
HD2008
HD2009










Hob: 2-2N: 220-240V - 50/60 Hz – 7.4 kW
2N: 380-415V - 50/60 Hz – 7.4 kW
1N: 220-240V - 50/60 Hz – 7.4 kW
1N: 220-240V - 50/60 Hz – 3.7 kW



OK!



Reageren! Lees voor gebruik het gebruiksaanwijzing.
Reageren! Read the instructions before use.
Reageren! Lisez attentivement le mode d'emploi avant utilisation.
Reageren! Lesen Sie die Bedienungsanleitung vor dem Gebrauch.
Reageren! Leggere attentamente le istruzioni per l'uso prima di utilizzare l'apparecchio.
Reageren! Læs brugsanvisningen grundigt, inden du bruger apparatet.




2N 380-415V 50/60Hz - 2x 16A

2 fase - 1 nul
2 phases - 1 neutral
2 Phasen - 1 Nullanschluss
2 phases et 1 neutre

Aderdoorsnede
Aderquerschnitt
Cross sectional area
Fil diamètre

4x2,5 mm²




1N 220-240V 50/60Hz - 1x 16A

1 fase - 1 nul
1 phase - 1 neutral
1 Phase - 1 Nullanschluss
1 phase et 1 neutre

Aderdoorsnede
Aderquerschnitt
Cross sectional area
Fil diamètre

3x2,5 mm²




Max 3720W

1N 220-240V 50/60Hz - 1x 32A

1 fase - 1 nul
1 phase - 1 neutral
1 Phase - 1 Nullanschluss
1 phase et 1 neutre

Aderdoorsnede
Aderquerschnitt
Cross sectional area
Fil diamètre

3x4 mm²




2-2N 230V 50Hz - 2x 16A

2 fase - 2 nulle
2 phases - 2 neutral
2 Phasen - 2 Nullanschlüsse
2 phases et 2 neutres

Aderdoorsnede
Aderquerschnitt
Cross sectional area
Fil diamètre

5x2,5 mm²



only NL/alleen NL

